

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																	
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +	
Acetaldehyde	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N	
Acetamide	N	N	N	N	N	N	N	N	N	N	N	N	N	R	R	R	N	
Acetate Solvent	R	R	R	R	R	R	R	N	R	N	N	N	N	R	N	R	N	
Acetic Acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	R	R	N	
Acetic Acid 20%	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R	
Acetic Acid 80%	N	R	R	R	N	N	N	N	N	N	N	N	N	R	R	R	N	
Acetic Acid, Glacial	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N	
Acetic Anhydride	R	R	R	N	R	R	N	N	R	N	N	N	N	R	N	R	N	
Acetone	R	R	R	R	N	N	N	N	N	R	R	N	N	R	N	R	N	
Acetyl Bromide	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	
Acetyl Chloride (dry)	R	R	R	N	R	N	N	R	R	N	N	N	N	R	N	R	R	
Acetylene	N	N	N	N	N	N	N	N	N	N	N	N	N	R	R	R	R	
Acrylonitrile	R	R	R	R	R	R	R	N	R	N	N	R	N	R	N	N	N	
Adipic Acid	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R	
Alcohols:Amyl	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	R	
Alcohols:Benzyl	R	R	R	R	R	R	N	R	R	N	N	N	N	R	R	R	R	
Alcohols:Butyl	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	R	
Alcohols:Diacetone	R	R	R	R	R	R	R	N	R	N	N	R	N	R	N	N	N	
Alcohols:Ethyl	R	R	R	R	N	N	N	N	N	R	R	N	N	R	N	N	N	
Alcohols:Hexyl	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N	
Alcohols:Isobutyl	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N	
Alcohols:Isopropyl	R	R	R	R	N	N	N	N	N	R	R	N	R	R	N	N	N	
Alcohols:Methyl	R	R	R	R	R	R	R	N	R	R	R	R	R	R	N	R	N	
Alcohols:Octyl	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	
Alcohols:Propyl	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	R	
Aluminum Chloride	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R	
Aluminum Chloride 20%	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N	
Aluminum Fluoride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	R	R	N	
Aluminum Hydroxide	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N	
Aluminum Nitrate	N	N	N	N	R	N	N	R	R	N	N	R	N	R	N	N	R	
Aluminum Potassium Sulfate 10%	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	R	
Aluminum Potassium Sulfate 100%	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																	
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +	
Alums	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N	
Amines	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N	
Ammonia 10%	R	R	R	R	R	R	N	N	R	N	N	R	N	R	N	R	N	
Ammonia, anhydrous	R	R	R	R	R	R	N	N	R	N	N	R	N	R	N	R	N	
Ammonia, liquid	R	R	R	R	R	R	N	N	R	N	N	R	N	R	N	R	N	
Ammonia Nitrate	N	N	N	N	N	N	N	N	R	N	N	N	N	R	N	R	N	
Ammonium Acetate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	
Ammonium Bifluoride	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R	
Ammonium Carbonate	R	R	R	R	R	R	N	R	R	R	R	R	N	R	R	R	R	
Ammonium Caseinate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	
Ammonium Chloride	N	N	N	N	R	R	N	R	R	N	N	R	R	R	R	R	R	
Ammonium Hydroxide	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R	
Ammonium Nitrate	R	R	R	R	R	R	N	R	R	N	N	R	N	R	R	R	R	
Ammonium Oxalate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	
Ammonium Persulfate	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R	
Ammonium Phosphate, Dibasic	N	N	N	N	N	N	N	R	R	N	N	N	N	N	R	R	N	
Ammonium Phosphate, Monobasic	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	
Ammonium Phosphate, Tribasic	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N	
Ammonium Sulfate	R	R	R	R	R	R	N	R	R	R	R	R	R	R	R	R	R	
Ammonium Sulfite	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	
Ammonium Thiosulfate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	
Amyl Acetate	R	R	R	R	R	R	R	N	R	N	N	N	N	R	N	R	N	
Amyl Alcohol	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	R	
Amyl Chloride	R	R	R	N	R	R	N	R	R	N	N	N	N	R	N	N	R	
Aniline	R	R	R	R	R	N	N	R	R	N	N	N	N	R	N	R	R	
Aniline Hydrochloride	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	
Antifreeze	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N	
Antimony Trichloride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N	
Aqua Regia (80% HCl, 20% HNO3)	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	N	N	
Arochlor 1248	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N	

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Aromatic Hydrocarbons	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Arsenic Acid	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Arsenic Salts	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Asphalt	N	N	N	N	R	R	R	R	R	N	N	R	R	R	R	R	R
Barium Carbonate	R	R	R	N	R	N	R	R	R	N	N	R	N	R	N	R	R
Barium Chloride	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	N
Barium Cyanide	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Barium Hydroxide	R	R	R	N	R	N	N	R	R	N	N	R	N	R	N	R	N
Barium Nitrate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Barium Sulfate	R	R	R	N	R	R	R	R	R	R	R	R	N	R	R	R	R
Barium Sulfide	N	N	N	N	R	N	N	R	R	N	R	R	R	R	N	N	R
Beer	R	R	R	R	R	R	R	R	R	N	N	R	R	R	R	R	R
Beet Sugar Liquids	N	N	N	N	R	R	N	R	R	N	N	R	N	R	N	N	R
Benzaldehyde	R	R	R	R	R	R	N	N	R	R	R	N	N	R	N	R	N
Benzene	R	R	R	R	R	R	N	R	R	R	R	N	N	R	R	R	R
Benzene Sulfonic Acid	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Benzoic Acid	R	R	R	R	R	R	N	R	R	N	N	R	R	R	R	R	R
Benzol	R	R	R	N	R	R	N	R	R	N	N	N	N	R	R	R	R
Benzonitrile	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Benzyl Chloride	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Bleaching Liquors	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Borax (Sodium Borate)	N	R	R	R	N	N	N	R	R	N	N	N	R	R	R	R	R
Boric Acid	R	R	R	N	R	N	N	R	R	N	R	R	N	R	N	R	R
Brewery Slop	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Bromine	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N
Butadiene	N	N	N	N	R	R	N	R	R	N	N	N	N	R	R	R	R
Butane	R	R	R	R	R	R	N	R	R	N	N	N	N	R	R	R	R
Butanol (Butyl Alcohol)	R	R	R	R	R	R	N	R	R	N	N	N	N	R	R	R	R
Butter	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Buttermilk	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Butyl Acetate	R	R	R	R	R	R	R	N	R	R	R	N	N	R	N	R	N
Butyl Amine	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Butyl Ether	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Butyl Phthalate	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Butylene	N	N	N	N	X^	X^	N	N	N	N	N	N	N	R	R	R	R
Butyric Acid	R	R	R	R	X^	X^	N	X^	N	N	N	N	R	R	R	R	N
Calcium Bisulfate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Calcium Bisulfide	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	R
Calcium Bisulfite	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	R
Calcium Carbonate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Calcium Chlorate	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	R
Calcium Chloride	R	R	R	R	R	N	N	R	R	N	R	N	N	R	N	R	R
Calcium Hydroxide	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	R	R
Calcium Hypochlorite	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Calcium Nitrate	R	R	R	R	R	R	N	R	R	N	N	R	N	R	R	R	R
Calcium Oxide	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	R
Calcium Sulfate	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	R	R
Calgon	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Cane Juice	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Carbolic Acid (Phenol)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	R
Carbon Bisulfide	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Carbon Dioxide (dry)	R	R	R	R	X^	X^	X^	N	N	N	N	N	N	R	R	R	R
Carbon Dioxide (wet)	R	R	R	R	R	R	N	R	R	N	N	R	N	R	R	R	R
Carbon Disulfide	R	R	R	N	R	R	N	R	R	N	N	N	N	R	R	R	R
Carbon Monoxide	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	R
Carbon Tetrachloride	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Carbon Tetrachloride (dry)	R	R	R	N	R	N	R	R	R	N	N	N	N	R	N	R	R
Carbon Tetrachloride (wet)	N	R	R	N	N	N	N	N	R	N	N	N	N	R	N	R	N
Carbonated Water	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Carbonic Acid	R	R	R	R	R	R	N	R	R	N	N	R	N	R	R	R	R
Catsup	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Chloric Acid	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Chlorinated Glue	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Chlorine (dry)	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Chlorine Water	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Chlorine, Anhydrous Liquid	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	N	N
Chloroacetic Acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Chlorobenzene (Mono)	R	R	R	R	R	R	R	R	R	R	R	N	N	R	R	R	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Chlorobromomethane	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Chloroform	R	R	R	R	R	R	R	R	R	R	R	N	N	R	R	R	N
Chlorosulfonic Acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Chocolate Syrup	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Chromic Acid 5%	N	R	R	R	N	N	N	R	N	N	N	N	N	R	N	R	R
Chromic Acid 10%	N	R	R	R	N	N	N	R	N	N	N	N	N	R	N	R	R
Chromic Acid 30%	N	N	N	N	N	N	N	R	N	N	N	N	N	R	N	R	R
Chromic Acid 50%	N	R	R	R	N	N	N	R	N	N	N	N	N	R	N	R	N
Chromium Salts	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Cider	N	N	N	N	N	N	N	N	N	N	N	N	R	R	N	N	R
Citric Acid	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	N
Citric Oils	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Clorox® Bleach (Sodium Hypochlorite)	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Coffee	R	N	N	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Copper Chloride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Copper Cyanide	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	R
Copper Fluoborate	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Copper Nitrate	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	R
Copper Sulfate 5%	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Copper Sulfate >5%	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Cream	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Cresols	N	N	N	R	N	N	N	N	N	N	N	N	N	R	R	N	R
Cresylic Acid	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	R
Cupric Acid	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Cyanic Acid	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Cyclohexane	R	R	R	R	R	R	R	R	R	R	R	N	N	R	R	R	R
Cyclohexanone	R	R	R	R	N	N	N	N	N	R	R	N	N	R	N	R	N
Detergents	N	R	R	R	N	N	N	R	R	N	N	N	R	R	R	R	R
Diacetone Alcohol	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Dichlorobenzene	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Dichloroethane	N	R	R	R	N	N	N	N	R	N	N	N	N	R	N	N	N
Diesel Fuel	R	R	R	R	R	R	R	R	R	R	N	R	N	R	R	R	R
Diethyl Ether	R	R	R	R	R	R	R	N	R	N	N	N	N	R	N	R	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Diethylamine	R	N	N	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Diethylene Glycol	R	R	R	R	R	R	N	R	R	N	N	N	N	R	N	N	N
Dimethyl Aniline	R	R	R	N	X^	X^	N	N	N	N	N	N	N	R	N	R	N
Dimethyl Formamide	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Diphenyl	R	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Diphenyl Oxide	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	N
Dyes	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Epsom Salts (Magnesium Sulfate)	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	R
Ethane	N	N	N	N	R	N	N	R	R	N	N	R	N	R	N	N	N
Ethanol	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Ethanolamine	R	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Ether	R	R	R	R	R	R	R	N	R	N	N	N	N	R	N	R	N
Ethyl Acetate	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Ethyl Benzoate	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Ethyl Chloride	R	R	R	R	R	R	R	R	R	N	N	N	N	R	R	R	N
Ethyl Ether	R	R	R	N	R	R	R	N	R	N	N	N	N	R	N	R	N
Ethyl Sulfate	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Ethylene Bromide	R	R	R	N	X^	X^	N	N	N	N	N	N	N	R	N	N	N
Ethylene Chloride	N	N	N	N	R	R	N	R	R	N	N	N	N	R	R	R	R
Ethylene Chlorohydrin	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Ethylene Diamine	N	N	N	N	X^	X^	N	N	N	N	N	N	N	R	R	R	R
Ethylene Dichloride	R	R	R	R	R	R	R	R	R	N	N	N	N	R	R	R	R
Ethylene Glycol	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R
Ethylene Oxide	R	R	R	R	R	N	N	N	R	N	N	N	N	R	N	N	N
Fatty Acids	R	R	R	R	R	R	N	R	R	N	N	R	N	R	N	N	R
Ferric Chloride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Ferric Nitrate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Ferric Sulfate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Ferrous Chloride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Ferrous Sulfate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R
Fluoboric Acid	N	R	R	N	N	N	N	X^	N	N	N	N	N	R	N	R	R
Fluorine	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Fluosilicic Acid	N	R	R	N	N	N	N	X^	N	N	N	N	N	R	N	R	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Formaldehyde 40%	N	R	R	R	N	N	N	R	R	N	N	N	R	R	R	R	N
Formaldehyde 10%	R	R	R	R	R	R	N	N	R	R	R	R	R	R	N	R	N
Formic Acid	N	R	R	N	N	N	N	N	R	N	N	N	N	R	N	R	N
Freon 113	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Freon 12	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	N
Freon 22	R	R	R	R	R	N	R	N	R	N	N	R	N	R	N	R	R
Freon TF	R	R	R	R	R	N	N	R	R	N	N	R	R	R	N	N	R
Freon® 11	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	R	R
Fruit Juice	R	R	R	R	R	R	N	R	R	R	R	R	N	R	N	N	R
Fuel Oil (#1 & #2)	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	N
Furan Resin	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Furfural	R	R	R	N	R	R	N	N	R	N	N	N	N	R	N	R	R
Gallic Acid	R	R	R	R	X^	N	N	N	N	N	N	N	N	R	N	R	R
Gasoline (high-aromatic)	R	R	R	N	R	N	N	R	R	N	R	R	N	R	N	R	R
Gasoline, leaded, ref.	R	R	R	R	R	R	N	R	R	R	R	R	R	R	R	R	R
Gasoline, unleaded	R	R	R	R	R	R	N	R	R	R	R	N	N	R	R	R	R
Gelatin	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	N	R
Glucose	R	R	R	R	R	R	R	R	R	N	N	R	R	R	R	R	N
Glue, P.V.A.	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Glycerin	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R
Glycolic Acid	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	R	R
Gold Monocyanide	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Grape Juice	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Grease	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	R
Heptane	R	R	R	R	R	R	R	R	R	N	N	N	N	R	R	R	R
Hexane	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R
Honey	R	R	R	R	R	R	N	R	R	N	N	R	N	R	N	N	R
Hydraulic Oil (Petro)	R	R	R	R	R	R	R	R	R	N	N	R	R	R	N	N	R
Hydraulic Oil (Synthetic)	R	R	R	R	R	R	R	R	R	N	N	R	N	R	N	N	R
Hydrazine	N	N	N	N	R	N	N	R	R	N	N	N	N	R	N	N	R
Hydrobromic Acid 20%	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Hydrobromic Acid 10%	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Hydrochloric Acid 20%	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	N	N
Hydrochloric Acid 37%	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	N	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Hydrochloric Acid 100%	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N
Hydrochloric Acid, Dry Gas	N	N	N	N	N	N	N	N	R	N	N	N	N	N	N	R	R
Hydrocyanic Acid	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	N
Hydrocyanic Acid (Gas 10%)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Hydrofluoric Acid 20%	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	R	N
Hydrofluoric Acid 50%	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	R	N
Hydrofluoric Acid 75%	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	R	R
Hydrofluoric Acid 100%	N	R	R	N	N	N	N	X^	N	N	N	N	N	R	N	N	N
Hydrofluosilicic Acid 10%	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Hydrofluosilicic Acid 20%	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	R	R
Hydrogen Gas	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	R
Hydrogen Peroxide 10%	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R
Hydrogen Peroxide 30%	N	R	R	R	N	N	N	N	N	N	N	N	N	R	R	R	R
Hydrogen Peroxide 50%	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Hydrogen Peroxide 100%	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Hydrogen Sulfide (aqua)	R	R	R	R	R	R	N	N	R	N	N	R	N	R	N	R	N
Hydrogen Sulfide (dry)	R	R	R	R	X^	X^	N	N	N	N	N	N	N	R	N	R	N
Hydroquinone	N	R	R	R	N	N	N	N	N	N	N	N	R	R	N	N	N
Hydroxyacetic Acid 70%	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N
Ink	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N
Iodine	N	N	N	N	N	N	N	X^	N	N	N	N	N	N	N	N	N
Iodine (in alcohol)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Iodoform	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Isooctane	N	N	N	N	X^	X^	X^	N	N	N	N	N	N	R	R	R	N
Isopropyl Acetate	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Isopropyl Ether	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Isotane	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Jet Fuel (JP3, JP4, JP5)	R	R	R	R	R	R	N	R	R	R	R	N	N	R	R	R	R
Kerosene	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R
Ketones	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Lacquer Thinners	R	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Lacquers	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Lactic Acid	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Lard	R	R	R	R	R	R	N	R	R	N	N	R	N	R	N	N	R
Latex	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Lead Acetate	N	R	R	R	N	N	N	N	R	N	N	N	N	R	N	R	R
Lead Nitrate	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Lead Sulfamate	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Ligroin	N	N	N	N	X^	N	N	N	N	N	N	N	N	R	N	N	R
Lime	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Linoleic Acid	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Lithium Chloride	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Lithium Hydroxide	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Lubricants	R	R	R	R	R	R	N	R	R	N	N	R	N	R	R	R	R
Lye: Ca(OH)2 Calcium Hydroxide	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	R	R
Lye: KOH Potassium Hydroxide	N	R	R	R	N	N	N	N	N	N	N	N	R	R	N	R	N
Lye: NaOH Sodium Hydroxide	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Magnesium Bisulfate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Magnesium Carbonate	R	R	R	N	R	R	N	R	R	N	N	R	N	R	N	N	N
Magnesium Chloride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Magnesium Hydroxide	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	R	R
Magnesium Nitrate	R	R	R	R	R	R	N	R	R	N	N	R	R	R	R	R	N
Magnesium Oxide	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Magnesium Sulfate (Epsom Salts)	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	R
Maleic Acid	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R
Maleic Anhydride	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Malic Acid	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Manganese Sulfate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	N
Mash	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Mayonnaise	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Melamine	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Mercuric Chloride (dilute)	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Mercuric Cyanide	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Mercurous Nitrate	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Mercury	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	N	R
Methane	R	R	R	R	X^	X^	N	N	N	N	N	N	N	R	N	N	N
Methanol (Methyl Alcohol)	R	R	R	R	R	R	R	N	R	R	R	R	R	R	N	R	N
Methyl Acetate	R	R	R	R	R	R	N	N	R	N	N	N	N	R	N	N	N
Methyl Acetone	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Methyl Acrylate	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Methyl Alcohol 10%	R	R	R	R	R	R	R	N	R	N	N	R	R	R	N	R	R
Methyl Bromide	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	N
Methyl Butyl Ketone	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Methyl Cellosolve	N	N	N	N	R	R	R	N	R	N	N	N	N	R	N	N	R
Methyl Chloride	R	R	R	R	R	N	R	R	R	N	N	N	N	R	N	R	N
Methyl Dichloride	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Methyl Ethyl Ketone	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Methyl Ethyl Ketone Peroxide	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Methyl Isobutyl Ketone	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Methyl Isopropyl Ketone	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Methyl Methacrylate	N	N	N	N	R	N	N	N	N	N	N	R	N	R	N	N	N
Methylamine	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Methylene Chloride	R	R	R	R	R	N	R	R	R	N	N	N	N	R	N	R	R
Milk	R	R	R	R	R	R	N	R	R	R	R	R	R	R	N	N	N
Mineral Spirits	R	R	R	R	N	N	N	N	N	N	N	N	N	R	R	R	R
Molasses	R	R	R	R	R	R	R	R	R	N	N	R	R	R	N	N	N
Monochloroacetic acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Monoethanolamine	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Morpholine	R	R	R	N	X^	X^	N	N	N	N	N	N	N	R	N	N	N
Motor oil	N	N	N	N	R	R	N	N	R	R	R	R	R	R	N	R	N
Mustard	N	R	R	R	N	N	N	N	R	N	N	N	N	R	N	N	R
Naphtha	R	R	R	R	R	R	R	R	R	N	N	R	N	R	R	R	R
Naphthalene	R	R	R	R	R	R	N	R	R	N	N	N	N	R	R	R	N
Natural Gas	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Nickel Chloride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Nickel Nitrate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Nickel Sulfate	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	N
Nitrating Acid (<15% H2SO4)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Nitrating Acid (>15% H2SO4)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Nitrating Acid (<1% Acid)	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Nitrating Acid (<15% HNO3)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Nitric Acid (5-10%)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	R
Nitric Acid (20%)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Nitric Acid (50%)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Nitric Acid (Concentrated)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Nitrobenzene	N	N	N	N	R	R	N	R	R	N	N	N	N	R	R	R	N
Nitrogen Fertilizer	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Nitromethane	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	R
Nitrous Acid	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	N
Nitrous Oxide	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Oils:Aniline	R	R	R	R	R	N	N	N	R	N	N	N	N	R	N	N	N
Oils:Anise	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Oils:Bay	N	N	N	N	R	N	N	N	N	N	N	N	N	R	N	N	R
Oils:Bone	N	N	N	N	R	N	N	R	R	N	N	N	N	R	N	N	R
Oils:Castor	N	N	N	N	R	R	R	R	R	R	R	R	R	R	N	N	N
Oils:Cinnamon	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Oils:Citric	R	R	R	R	R	R	R	R	R	N	N	R	N	R	N	N	N
Oils:Clove	R	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Oils:Coconut	R	R	R	N	R	R	N	R	R	N	N	R	N	R	N	N	R
Oils:Cod Liver	R	R	R	N	R	R	N	R	R	N	N	R	N	R	N	N	R
Oils:Corn	R	R	R	R	R	R	N	R	R	N	N	R	N	R	N	N	R
Oils:Cottonseed	R	R	R	N	R	R	R	R	R	N	N	R	N	R	R	R	N
Oils:Creosote	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Oils:Diesel Fuel (20, 30, 40, 50)	R	R	R	R	R	R	N	R	R	N	N	R	N	R	R	R	R
Oils:Fuel (1, 2, 3, 5A, 5B, 6)	R	R	R	R	R	N	R	R	R	N	N	R	N	R	N	R	N
Oils:Ginger	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	R
Oils:Hydraulic Oil (Petro)	R	R	R	R	R	R	R	R	R	N	N	R	N	R	N	N	R
Oils:Hydraulic Oil (Synthetic)	R	R	R	R	R	R	R	R	R	N	N	R	N	R	N	N	R
Oils:Lemon	N	N	N	N	R	R	N	R	R	N	N	N	N	R	N	N	R
Oils:Linseed	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	N
Oils:Mineral	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Oils:Olive	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Oils:Orange	R	N	N	R	R	R	N	N	N	N	N	N	N	R	N	N	R
Oils:Palm	N	N	N	N	R	N	N	R	R	N	N	R	N	R	N	N	R
Oils:Peanut	N	N	N	N	R	R	N	R	R	N	N	R	N	R	N	N	N
Oils:Peppermint	N	N	N	N	R	N	N	R	R	N	N	N	N	R	N	N	R
Oils:Pine	N	N	N	N	R	R	N	R	R	N	N	N	N	R	N	N	R
Oils:Rapeseed	N	N	N	N	R	N	N	R	R	N	N	N	N	R	N	N	R
Oils:Rosin	R	R	R	N	R	R	N	R	R	N	N	N	N	R	N	N	R
Oils:Sesame Seed	N	N	N	N	R	N	N	R	R	N	N	R	N	R	N	N	R
Oils:Silicone	R	R	R	R	R	R	N	R	R	R	R	R	R	R	R	R	R
Oils:Soybean	R	R	R	R	R	R	N	R	R	N	N	R	N	R	N	N	R
Oils:Sperm (whale)	N	N	N	N	R	N	N	R	R	N	N	N	N	R	N	N	R
Oils:Tanning	N	N	N	N	R	N	N	N	N	N	N	N	N	R	N	N	R
Oils:Transformer	N	N	N	N	R	R	N	R	R	N	N	R	N	R	N	N	R
Oils:Turbine	N	N	N	N	R	R	N	R	R	N	N	R	N	R	N	N	R
Oleic Acid	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	N
Oleum 25%	N	R	R	N	N	N	N	N	N	N	N	N	N	R	R	R	N
Oleum 100%	N	N	N	N	N	N	N	N	N	N	N	N	N	R	R	R	R
Oxalic Acid (cold)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	R
Ozone	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Palmitic Acid	R	R	R	N	X^	X^	N	N	N	N	N	N	N	R	N	N	R
Paraffin	R	R	R	R	R	R	R	R	R	N	N	R	N	R	N	N	N
Pentane	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N
Perchloric Acid	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Perchloroethylene	R	R	R	R	R	N	N	R	R	N	N	N	N	R	N	R	R
Petrolatum	R	N	N	R	R	N	N	N	N	N	N	R	N	R	N	N	R
Petroleum	N	N	N	N	R	N	N	R	R	N	N	N	N	R	N	N	R
Phenol (10%)	R	R	R	N	R	R	N	R	R	N	N	N	N	R	R	R	N
Phenol (Carbolic Acid)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	N
Phosphoric Acid (<40%)	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Phosphoric Acid (>40%)	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Phosphoric Acid (crude)	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Phosphoric Acid (molten)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Phosphoric Acid Anhydride	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Phosphorus	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Phosphorus Trichloride	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Photographic Developer	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Photographic Solutions	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R	R
Phthalic Acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Phthalic Anhydride	R	R	R	N	X^	X^	N	N	N	N	N	N	N	R	N	N	N
Picric Acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	R
Plating Solutions, Antimony Plating 130°F	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Plating Solutions, Arsenic Plating 110°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Brass Plating: High-Speed Brass Bath 110°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Brass Plating: Regular Brass Bath 100°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Bronze Plating: Cu-Cd Bronze Bath R.T.	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Bronze Plating: Cu-Sn Bronze Bath 160°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Bronze Plating: Cu-Zn Bronze Bath 100°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Cadmium Plating: Cyanide Bath 90°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Plating Solutions, Cadmium Plating: Fluoborate Bath	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Plating Solutions, Chromium Plating: Barrel Chrome Bath 95°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Plating Solutions, Chromium Plating: Black Chrome Bath 115°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Chromium Plating: Chromic-Sulfuric Bath 130°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Chromium Plating: Fluoride Bath 130°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Chromium Plating: Fluosilicate Bath 95°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Copper Plating (Acid): Copper Fluoborate Bath 120°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Copper Plating (Acid): Copper Sulfate Bath R.T.	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Plating Solutions, Copper Plating (Cyanide): Copper Strike Bath 120°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Copper Plating (Cyanide): High-Speed Bath 180°F	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Plating Solutions, Copper Plating (Cyanide): Rochelle Salt Bath 15N°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Plating Solutions, Copper Plating (Misc): Copper (Electroless)	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N
Plating Solutions, Copper Plating (Misc): Copper Pyrophosphate	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	N
Plating Solutions, Gold Plating: Acid 75°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Plating Solutions, Gold Plating: Cyanide 150°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Plating Solutions, Gold Plating: Neutral 75°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Indium Sulfamate Plating R.T.	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Iron Plating: Ferrous Am Sulfate Bath 150°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Iron Plating: Ferrous Chloride Bath 190°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Iron Plating: Ferrous Sulfate Bath 150°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Iron Plating: Fluoborate Bath 145°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Iron Plating: Sulfamate 140°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Iron Plating: Sulfate-Chloride Bath 160°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Lead Fluoborate Plating	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Nickel Plating: Electroless 200°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Nickel Plating: Fluoborate 100-170°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Nickel Plating: High-Chloride 130-160°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Nickel Plating: Sulfamate 100-140°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Nickel Plating: Watts Type 115-	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Rhodium Plating 12N°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Plating Solutions, Silver Plating 8N-12N°F	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Plating Solutions, Tin-Fluoborate Plating 100°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Tin-Lead Plating 100°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Zinc Plating: Acid Chloride 140°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Zinc Plating: Acid Fluoborate Bath R.T.	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Plating Solutions, Zinc Plating: Acid Sulfate Bath 15N°F	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Plating Solutions, Zinc Plating: Alkaline Cyanide Bath R.T.	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Potash (Potassium Carbonate)	N	N	N	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Potassium Bicarbonate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Potassium Bromide	R	R	R	R	R	N	N	R	R	N	N	R	R	R	N	R	R
Potassium Chlorate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R
Potassium Chloride	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Potassium Chromate	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Potassium Cyanide Solutions	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	R	R
Potassium Dichromate	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	N
Potassium Ferricyanide	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	N	R
Potassium Ferrocyanide	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Potassium Hydroxide (Caustic Potash)	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	R
Potassium Hypochlorite	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	R
Potassium Iodide	N	R	R	N	N	N	N	R	R	N	N	N	N	R	R	R	N
Potassium Nitrate	N	R	R	R	N	N	N	R	R	N	N	N	R	R	R	R	R
Potassium Oxalate	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Potassium Permanganate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Potassium Sulfate	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	R
Potassium Sulfide	N	N	N	N	R	N	N	R	R	N	N	R	N	R	N	R	N
Propane (liquefied)	R	R	R	R	R	R	R	R	R	N	N	R	N	R	N	N	N
Propylene	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Propylene Glycol	R	R	R	R	N	N	N	N	N	R	R	N	N	R	N	N	R
Pyridine	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	R	N
Pyrogalllic Acid	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Resorcinol	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Rosins	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Rum	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Rust Inhibitors	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Salad Dressings	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Salicylic Acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Salt Brine (NaCl saturated)	N	R	R	R	N	N	N	N	N	N	N	N	N	R	R	R	N
Sea Water	N	N	N	N	N	N	N	R	R	N	N	N	N	N	R	R	R
Shellac (Bleached)	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Shellac (Orange)	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Silicone	N	N	N	N	N	N	N	R	R	N	N	N	N	R	R	R	R
Silver Bromide	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Silver Nitrate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	N
Soap Solutions	R	R	R	R	R	N	R	R	R	N	R	R	R	R	N	R	N
Soda Ash (see Sodium Carbonate)	N	N	N	N	R	N	N	R	R	N	N	R	N	R	N	R	N
Sodium Acetate	R	R	R	R	R	R	R	N	R	N	N	R	N	R	N	R	R
Sodium Aluminate	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Sodium Benzoate	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Sodium Bicarbonate	R	R	R	R	R	N	N	R	R	N	N	R	R	R	N	R	R
Sodium Bisulfate	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Sodium Bisulfite	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	N
Sodium Borate (Borax)	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Sodium Bromide	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Sodium Carbonate	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	R
Sodium Chlorate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Sodium Chloride	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Sodium Chromate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R
Sodium Cyanide	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	N
Sodium Ferrocyanide	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Sodium Fluoride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	N	N
Sodium Hydrosulfite	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Sodium Hydroxide (20%)	N	R	R	R	N	N	N	N	R	N	N	N	N	R	N	R	N
Sodium Hydroxide (50%)	N	N	N	N	N	N	N	N	R	N	N	N	N	R	N	R	N
Sodium Hydroxide (80%)	N	R	R	R	N	N	N	N	R	N	N	N	N	R	N	R	N
Sodium Hypochlorite (<20%)	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Sodium Hypochlorite (100%)	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Sodium Hyposulfate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Sodium Metaphosphate	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	N
Sodium Metasilicate	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Sodium Nitrate	N	R	R	R	N	N	N	N	N	N	N	N	R	R	R	R	R
Sodium Perborate	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Sodium Peroxide	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	R
Sodium Polyphosphate	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	N	N
Sodium Silicate	R	R	R	R	R	R	N	R	R	N	N	R	N	R	R	R	R
Sodium Sulfate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	N
Sodium Sulfide	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Sodium Sulfite	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Sodium Tetraborate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Sodium Thiosulfate (hypo)	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	N
Sorghum	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Soy Sauce	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Stannic Chloride	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	N
Stannic Fluoborate	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Stannous Chloride	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Starch	N	N	N	N	N	N	N	N	N	N	N	N	R	R	N	N	N
Stearic Acid	R	R	R	R	R	R	N	R	R	N	N	R	N	R	N	N	N
Stoddard Solvent	R	R	R	R	R	R	N	R	R	N	N	N	N	R	R	R	N
Styrene	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Sugar (Liquids)	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Sulfate (Liquors)	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	N	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GPI Product Lines																
	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS##	DP Insertion +
Sulfur Chloride	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Sulfur Dioxide	N	N	N	N	R	R	N	R	R	N	N	R	N	R	R	R	N
Sulfur Dioxide (dry)	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	N
Sulfur Hexafluoride	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Sulfur Trioxide	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R
Sulfur Trioxide (dry)	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Sulfuric Acid (<10%)	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Sulfuric Acid (10-75%)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N
Sulfuric Acid (75-100%)	N	N	N	N	N	N	N	R	R	N	N	N	N	N	N	R	R
Sulfuric Acid (hot concentrated)	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Sulfuric Acid (cold concentrated)	N	R	R	N	N	N	N	N	N	N	N	N	N	R	R	R	N
Sulfurous Acid	N	R	R	R	N	N	N	R	R	N	N	N	N	R	R	R	R
Sulfuryl Chloride	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Tallow	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Tannic Acid	N	R	R	R	N	N	N	R	R	N	N	N	R	R	N	R	R
Tanning Liquors	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Tartaric Acid	N	N	N	N	N	N	N	R	R	N	N	N	N	N	R	R	N
Tetrachloroethane	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	N	N
Tetrachloroethylene	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Tetrahydrofuran	R	R	R	R	R	N	N	N	R	N	N	N	N	R	N	R	R
Tin Salts	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N	N
Toluene (Toluol)	R	R	R	R	R	R	R	N	R	R	R	N	N	R	N	R	R
Tomato Juice	N	N	N	N	N	N	N	R	R	N	N	N	N	R	R	R	R
Trichloroacetic Acid	N	N	N	N	N	N	N	N	R	N	N	N	N	N	N	R	N
Trichloroethane	R	R	R	R	R	N	N	R	R	N	N	N	N	R	N	N	N
Trichloroethylene	R	R	R	R	R	N	N	N	N	N	N	N	N	R	N	R	N
Trichloropropane	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Tricresylphosphate	N	R	R	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Triethylamine	N	N	N	N	R	N	N	N	R	N	N	R	N	R	N	N	R
Trisodium Phosphate	R	R	R	R	X^	N	N	N	N	N	N	N	N	R	N	R	N
Turpentine	R	R	R	R	R	R	N	R	R	N	N	N	N	R	R	R	R
Urea	R	R	R	R	R	R	N	R	R	N	N	N	N	R	R	R	N

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase

GPI product lines approved for specific chemicals

Meter Models R=Recommended N=Not recommended	GNT Model	GNP Model	GSCP Model	GSCPS Model	G2 Stainless	G2 Aluminum	G2 Brass	G2 PVDF	G2 PVDF #	A1 Aluminum	A1 Nylon	TM Series 0.5-2"	TM Series 3-4"	OM Stainless**	OM Aluminum*	OM 1" PPS ##	DP Insertion +
Uric Acid	N	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	N
Urine	N	N	N	N	N	N	N	R	R	N	N	N	N	R	N	N	R
Varnish	R	R	R	R	N	N	N	N	N	N	N	N	N	R	N	N	R
Vegetable Juice	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Vinegar	R	R	R	R	R	N	N	R	R	N	N	R	R	R	N	R	R
Vinyl Acetate	N	N	N	N	R	R	N	R	R	N	N	N	N	R	N	N	R
Vinyl Chloride	R	R	R	R	R	R	N	R	R	N	N	N	N	R	N	N	R
Water, Acid, Mine	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	R	R
Water, Deionized	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	R	R
Water, Distilled	R	R	R	R	R	N	R	R	R	N	N	R	N	R	N	R	N
Water, Fresh	R	R	R	R	R	N	R	R	R	N	N	R	N	R	N	R	N
Water, Salt	R	R	R	R	R	N	N	R	R	N	N	R	N	R	N	R	R
Weed Killers	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	R
Whey	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Whiskey & Wines	N	N	N	N	R	N	R	R	R	N	R	R	R	R	N	N	R
White Liquor (Pulp Mill)	N	R	R	N	N	N	N	R	R	N	N	N	N	R	N	N	R
White Water (Paper Mill)	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	N	N
Xylene	R	R	R	R	R	R	R	R	R	N	N	N	N	R	R	N	R
Zinc Chloride	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R
Zinc Hydrosulfite	N	N	N	N	N	N	N	N	N	N	N	N	N	R	N	R	N
Zinc Sulfate	N	R	R	R	N	N	N	R	R	N	N	N	N	R	N	R	R

*OM Aluminum with PPS and Viton materials

**OM Stainless and PTFE(Teflon) materials

+ DP Insertion Stainless, PVDF, and Viton

OM PPS with PTFE(Teflon) materials

G2 PVDF w/Teflon O-rings available for purchase